


DE-R 299 Diffractive Optical Element



- **Element Number:** DE-R 299
- **Current Product Revision:** A
- **Description:** Cross – 75 @ 650
- **Number of Spots on Line:** 1501
- **Substrate Material:** : Polymethyl Methacrylate (PMMA)
- **Size (Ø x Thickness):** 8 x 1 mm
- **Design Wavelengths:** 635 nm
- **Recommended Wavelength Range:** 580-690 nm
- **Minimum Recommended Beam Diameter:** 2-3 mm

Within the recommended wavelength range, the zeroth order is not brighter than the rest of the cross. Pattern size and pattern angles and the intensity in the undiffracted central spot ('zero order intensity', see reverse page) will vary most with the wavelength.


Diffraction efficiencies given on this datasheet have been measured using elements of product revision A.

Pattern Geometry and Diffraction Angles

Wavelength	Pattern Size @ 100 mm Distance	Pattern Angle
	a	α
450 nm	93 mm	50°
515 nm	110 mm	58°
532 nm	115 mm	60°
635 nm	148 mm	73°
650 nm	154 mm	75°
730 nm	187 mm	86°
780 nm	214 mm	94°
808 nm	232 mm	98°

MOUNTED VERSION

For testing or setups under laboratory conditions we offer a version mounted in 12.7 mm stainless steel frame for use with standard laboratory holders.




Thorlabs 8 mm steel lens adapter

COLLIMATED / CONVERGING LASER

The laser can be collimated for long range use or converging for a fixed working distance.

Please note that the size/thickness of each spot or line depends on the focusing of the laser.

Setup




Laser diodes are the most common light source to be used with diffractive optical elements, but other laser light sources may also be used.

The DOEs are best used with collimated or convergent laser sources. The microstructure surface should be oriented towards the laser.

The 0-order spot is equivalent in size and shape to the original beam, but its power is attenuated.

Diffraction Zero Order Intensity:

Wavelength	0-Order Intensity
450	27%
520	9.0%
532	6.1%
593	0.5%
638	0.4%
651	0.7%
687	1.6%



HOLOEYE Photonics AG
Volmerstr. 1
12489 Berlin, Germany
contact@holoeye.com
www.holoeye.com



Pioneers in Photonic Technology